

TECHSPEC<sup>®</sup> 20mm - 30mm Length, C-Mount Fine Focus Tube



Stock **#58-756** 12 In Stock

-

1

+

C\$165<sup>.20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | C\$165.20 each                |
| Qty 5-9        | C\$146.16 each                |
| Qty 10-25      | C\$134.96 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                        |
|----------------------------------|------------------------|
| Fine Focus Tube                  | Type:                  |
| Extension Tube (Adjustable)      | Function:              |
| Physical & Mechanical Properties |                        |
| 20.0 - 30.0                      | Extension Length (mm): |

|      |                         |
|------|-------------------------|
| 30.0 | Outer Diameter (mm):    |
| 18.0 | Clear Aperture CA (mm): |
| 18.0 | Inner Diameter (mm):    |

| Threading & Mounting |                |
|----------------------|----------------|
| M18 x0.5             | Barrel Thread: |
| C-Mount              | Thread Type:   |

| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 235:                  |

## Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

**Note:** Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

## Technical Information

