

[« See all 102 Products in Family](#)

[All Products](#) / [Laser Optics](#) / [Laser Lenses](#) / [Plano-Convex \(PCX\) Laser Lenses](#)
/ [633nm Laser Line Coated Plano-Convex \(PCX\) Lenses](#)

TECHSPEC®

25.0mm Diameter x 100.0mm FL, 633nm V-Coat, PCX Lens



Stock #65-507 **8 In Stock** [Other Coating Options](#)

1 C\$82^{.60}

ADD TO CART

633nm Laser Line Coated Plano-Convex (PCX) Lenses



Volume Pricing	
Qty 1-9	C\$82.60 each
Qty 10-25	C\$74.90 each
Qty 26-49	C\$66.15 each
Need More?	Request Quote

Product Downloads	
STEP:stp	Curve:pdf
PDF Drawing:pdf	
ISO 10110 Drawing	
IGES:igs	Zemax:zar
Zemax:zip	Zemax:zmx
eDrawing:eprt	Code V:seq
EO Spec Sheet	Download All

General			
Type:	Plano-Convex Lens		
Physical & Mechanical Properties			
Diameter (mm):	25.00 +0.0/-0.025	Centering (arcmin):	<1
Center Thickness CT (mm):	4.30 ±0.10	Edge Thickness ET (mm):	2.77
Clear Aperture CA (mm):	24	Bevel:	Protective as needed
Optical Properties			
Effective Focal Length EFL (mm):	100.00 @ 587.6nm	Back Focal Length BFL (mm):	97.17
Coating:	Laser V-Coat (633nm)	Coating Specification:	R _{abs} <0.25% @ 633nm
Substrate: ⓘ	N-BK7	Surface Quality:	40-20
Power (P-V) @ 632.8nm:	1.5λ	Irregularity (P-V) @ 632.8nm:	λ/4
Focal Length Tolerance (%):	±1	Radius R₁ (mm):	51.68
f/#:	4.00	Numerical Aperture NA:	0.13
Design Wavelength DWL (nm):	633	Damage Threshold, By Design: ⓘ	5 J/cm ² @ 633nm, 10ns

Regulatory Compliance

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

Reach 235: [Compliant](#)

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- <0.25% Reflection at 633nm for HeNe Applications
- BBAR Coating Options Also Available: [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- [405nm](#), [532nm](#), 633nm, [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered


TECHSPEC® 633nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 633nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [785nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information

Related Products



Laser Optics



Laser Sources



Arcturus® HeNe Beam Expanders



633nm Laser Line Coated Fused Silica PCX Lenses

Frequently Purchased Together



#33-425 - LightPath 354125 | 11mm Dia., 0.50 NA, BBAR (350-700nm), Molded Aspheric Lens
C\$166.60



#47-919 - 25mm Dia. x -100mm FL, VIS 0° Coated, Double-Concave Lens
C\$71.40









#55-178 - ¼-20 x ½" SHCS, 50/Pack
C\$29.05



#65-467 - 25.0mm Diameter x 100.0mm FL, 405nm V-Coat, PCX Lens
C\$82.60

Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
	25.0/25.4mm Optic Dia., SM1 Thin Mount, M4	Fixed		#13-787	C\$29.40 Request Quote	4 In Stock <input type="text" value="1"/>
	25.0/25.4mm Optic Dia., SM1 Thin Mount, 8-32	Fixed		#13-788	C\$29.40 Request Quote	20+ In Stock <input type="text" value="1"/>
	25.0mm Optic Dia., Optic Mount	Fixed		#64-560	C\$45.85 Request Quote	CONTACT US <input type="text" value="1"/>
	25mm Thin Inner Single Optic Mount	Fixed		#38-755	C\$57.40 Request Quote	20+ In Stock <input type="text" value="1"/>
	30mm Cage 25/25.4mm Diameter Lens Mount	Fixed		#85-587	C\$60.90 Request Quote	20+ In Stock <input type="text" value="1"/>
	30mm Cage 25/25.4mm Diameter Thick Lens Mount	Fixed		#85-588	C\$64.05 Request Quote	20+ In Stock <input type="text" value="1"/>
	25/30mm Cage 25mm Diameter Lens Mount	Fixed		#85-678	C\$64.05 Request Quote	3 In Stock <input type="text" value="1"/>
	25.0/25.4mm Optic Dia., L-Slot Direct Mount	Fixed		#36-410	C\$95.20 Request Quote	20+ In Stock <input type="text" value="1"/>
	25.0/25.4mm Optic Dia., Side Flange Direct Mount	Fixed		#36-414	C\$99.40 Request Quote	20+ In Stock <input type="text" value="1"/>
	25/25.4mm Diameter, T-Mount Thin Optic Mount	Fixed		#52-292	C\$100.80 Request Quote	CONTACT US <input type="text" value="1"/>
	25mm Thin Inner Pair Optic Mounts	Fixed		#11-052	C\$112.70 Request Quote	5 In Stock <input type="text" value="1"/>
	25mm Thick Inner Pair Optic Mounts	Fixed		#11-054	C\$112.70 Request Quote	16 In Stock <input type="text" value="1"/>
	25.0/25.4mm Optic Dia., L-Slot and Rotation Direct Mount	Adjustable - Rotary		#36-411	C\$142.80 Request Quote	5 In Stock <input type="text" value="1"/>

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	25.0/25.4mm Optic Dia., X-Y Translating Optic Mount	Adjustable - Linear (XY)		#62-956	C\$386.40 Request Quote	CONTACT US 1 
MORE+ 	25.0/25.4mm Optic Dia., X-Y-Z Translating Optic Mount	Adjustable - Linear (XYZ)		#62-959	C\$756.00 Request Quote	6 In Stock 1 
MORE+ 	25.0/25.4mm Optic Dia., 5 Axes Optical Mount	Adjustable - Linear (XYZ) & Tip-Tilt		#13-776	C\$1,057.00 Request Quote	2 In Stock 1 

Check out our full selection of mounts [here](#).

Resources

Media Type

- Application Note
- Technical Tool
- Video
- FAQ
- Trending in Optics
- Glossary
- Scientific Paper
- Published Article

APPLICATION NOTE

An Introduction to Optical Coatings

TECHNICAL TOOL

Gaussian Beams Calculator

VIDEO

Polarization Directed Flat Lenses Product Review

FAQ

What is the best lens for focusing or collimating th...

TRENDING IN OPTICS

Free-Space Optical Communication

APPLICATION NOTE

Common Laser Optics Materials

[View More](#)