

[See all 2 Products in Family](#)

25.4mm Dia. 5°, 1030nm Highly-Dispersive Broadband Ultrafast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



Stock #12-328 **12 In Stock**

⊖ 1 ⊕ C\$1,120⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-3	C\$1,120.00 each
Qty 4-7	C\$994.00 each
Qty 8+	C\$882.00 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Yb:doped 1st Harmonic **Typical Applications:**

HD120 **Model Number:**

Physical & Mechanical Properties

10 ±5	Wedge Angle (arcmin):
80	Clear Aperture (%):
Commercial Polish	Back Surface:
25.40 +0.0/-0.1	Diameter (mm):
6.35 ±0.2	Thickness (mm):

Optical Properties

99.9 (typical, p-polarization)	Reflection at DWL (%):
R _{avg} >99.8%, GDD = -200 fs ² @ 950 - 1120nm (p-polarization) R _{abs} >99.9% @ 1030nm (typical, p-polarization)	Coating Specification:
-200fs ² @ 950 - 1120nm	GDD Specification:
950 - 1120	Wavelength Range (nm):
M10	Irregularity (P-V) @ 632.8nm:
Dielectric	Coating Type:
Ultrafast (950-1120nm)	Coating:
1030	Design Wavelength DWL (nm):
5	Angle of Incidence (°):
Fused Silica (Coming 7980)	Substrate: <input type="checkbox"/>
>0.1 J/cm ² for 190 fs @ 1 kHz rep rate @ 1030nm	Damage Threshold, Reference: <input type="checkbox"/>

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:


Product Details

- Negative GDD of -200 fs² at 5° AOI
- >99.8% Reflection (p-polarization) between 950 - 1120nm
- Designed for Pulse Compression of Yb:doped Fiber Lasers
- Broadband Ultrafast Chirped Coating

UltraFast Innovations (UFI) 1030nm Highly-Dispersive Broadband Ultrafast Mirrors are used for pulse compression and dispersion compensation of near infrared (NIR) ultrafast pulses, such as from Yb:doped fiber lasers. These mirrors provide a minimum reflectance of 99.8% within their wavelength range and a typical reflectance of >99.9% at their design wavelength of 1030nm. Their multilayer chirped ultrafast coating is optimized to provide dispersive optical interference as well as a negative group delay dispersion (GDD) of -200fs² across their broad wavelength range. UFI 1030nm Highly-Dispersive Broadband Ultrafast Mirrors are designed to provide a high degree of control over beam stability, as well as control of third and higher-order dispersions. The 5° angle of incidence is ideal for maximizing the number of reflections between a pair of ultrafast mirrors in tight spaces, such as intra-cavity applications.

Standard imperial sizes of ½" or 1" (12.7mm or 25.4mm) are available; please contact us if your laser system requires a custom size, wavelength, or ultrashort pulses and we would be happy to find the right solution for your application.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
