

[See all 32 Products in Family](#)

**TECHSPEC® 25.4mm Dia. x 6.35mm 532/630-655/1064nm, Dual Band Laser Mirror**



Stock #26-927 **20+ In Stock**

⊖ 1 ⊕ C\$281<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$281.40 each
Qty 6-25	C\$267.40 each
Qty 26-49	C\$256.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

>90 **Clear Aperture (%):**

Commercial Polish	<b>Back Surface:</b>
25.40 +0/-0.1	<b>Diameter (mm):</b>
6.35 ±0.10	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
10-5	<b>Surface Quality:</b>
99.5	<b>Reflection at DWL (%):</b>
<b>Coating Specification:</b> R <sub>avg</sub> ≥99.50% @ 532nm & 1064nm @ 45° AOI R <sub>avg</sub> ≥80% @ 630 – 655nm @ 45° AOI	
M10	<b>Surface Flatness (P-V):</b>
Dielectric	<b>Coating Type:</b>
Laser Mirror (532, 635, 650, 1064nm)	<b>Coating:</b>
532, 635, 650, 1064	<b>Design Wavelength DWL (nm):</b>
45	<b>Angle of Incidence (°):</b>
<b>Fused Silica</b> (Coming 7980)	<b>Substrate:</b> <input type="checkbox"/>
Not Specified	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>

<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- >99% Reflectivity at Design Wavelengths
- 10-5 Surface Quality for Sensitive Laser Applications
- 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
- [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Dual Band Laser Line Mirrors feature high reflectivity, excellent surface quality, and precision surface flatness to minimize scattering effects. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in a variety of standard sizes. TECHSPEC® Dual Band Laser Line Mirrors are ideal for beam steering applications in both laboratory and OEM laser systems. These mirrors are available in a 532/1064nm, 635-670/1064nm, and 800/1030nm dual band coating options for Nd:YAG lasers and red and green guide beams.