


[See all 4 Products in Family](#)

## 25mm Dia. Metal Velvet™ Panel

See More by [Acktar](#)



Stock #37-832 **14 In Stock**

⊖ 1 ⊕ C\$93.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | C\$93.80 each                 |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

MP-25-3 **Model Number:**

**Note:**  
Ships with a low outgassing adhesive sticker that can be applied to the back surface

### Physical & Mechanical Properties

25.00 **Diameter (mm):**

Panel **Construction:**

60 **Adhesive Thickness (µm):**

1.20 **Thickness (mm):**

## Optical Properties

Metal Velvet™ **Coating:**

0.3 - 14 **Wavelength Range (µm):**

## Material Properties

99.5 - 99.7 (0 - 10° AOI) **Absorbance (%):**

## Environmental & Durability Factors

-50 to 150 **Operating Temperature (°C):**

Light, do not touch **Abrasion Resistance:**

ML-C-48497A **Humidity Resistance:**

## Regulatory Compliance

**RoHS 2015:**  
Compliant

**Certificate of Conformance:**  
View

**Reach 247:**  
Compliant

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Mountable Acktar Spectral Black™, Metal Velvet™, and Hexa-Black™ Technologies
- High Performance from UV to MMR and UV to LWIR
- Low Hemispherical Reflectance

Acktar Light Absorbent Panels are the optimum solution for absorbent black out materials. Light Absorbent Panels are easily integrated into an optical system using either an optical mount compatible with 25mm optics or the included adhesive sticker. With specular absorbance up to 99.9%, Spectral Black™ and Metal Velvet™ panels offer superior light absorption performance. The Hexa-Black™ versions feature wide-band absorption at grazing angles out to 88°. Acktar Light Absorbent Panels are typically used as black out materials and are ideal for Raman Spectroscopy, Endoscopy, Laser Beam Dumps, and many other applications.

**Note:** Larger sizes and custom options are available upon request by [contacting technical support](#). All panels have no adhesive pre-applied to the back surface. Each panel ships with an optional adhesive sticker that can be applied to the back surface of the panel.

## Technical Information

