

TECHSPEC[®] 25mm Dia x 40mm FL 3-5μm Coated, Hybrid Ge Aspheric Lens



Stock #68-264 20+ In Stock

-

1

+

C\$2,037^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,037.00 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

Physical & Mechanical Properties

25.00 +0.0/-0.1

Diameter (mm):

≤5

Centering (arcmin):

24.0

Clear Aperture CA (mm):

Edge Thickness ET (mm):

1.35	
2.10 ±0.10	Center Thickness CT (mm):
Protective as needed	Bevel:
Diamond Turned	Edges:
Concave	Shape of Back Surface:

Optical Properties

40.00 @ 4000nm	Effective Focal Length EFL (mm):
0.31	Numerical Aperture NA:
38.32	Back Focal Length BFL (mm):
Germanium (Ge)	Substrate: ☐
4000	Aspheric Design Wavelength (nm):
λ/6	Asphere Figure Error, RMS @ 632.8nm:
BBAR (3000-5000nm)	Coating:
R _{avg} <3.0% @ 3 - 5μm	Coating Specification:
0.3	Surface Accuracy, P-V (μm):
60-40	Surface Quality:
1.61	f/#:
52	Radius R ₂ (mm):
3000 - 5000	Wavelength Range (nm):
Infinite	Conjugate Distance:


Regulatory Compliance


Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Color Corrected for 3 – 5μm
 - Near Diffraction Limited Focusing Performance
 - Full Prescription Data Available
 - Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our [customer service team](#).
 - Edmund Optics has limited remaining inventory of this part number and no raw material available to supply more once this is depleted. Please contact our Product Support Engineers to help with an alternate solution for your needs. Customer Service can provide you the latest price and availability.
- Our TECHSPEC® Germanium Infrared (IR) Hybrid Aspheric Lenses provide diffraction limited focusing performance at any wavelength in the 3 – 5μm region, and near diffraction limited performance when used over the entire 3 -5μm spectral range. They are ideal for integration into imaging applications, FTIR spectrometers, or any Mid-Wave IR application utilizing a broad band light source.
- Each hybrid aspheric lens is coated for >95% transmission for the most efficient use of costly infrared illumination. However, transmission is limited by the inherent diffraction efficiency of the aspheric surface, yielding lower overall transmission at the extremes of the design spectral band. For custom design or coating options, please contact our [Sales Department](#).

Technical Information





Special Handling

Germanium Optics Handling and Cleaning Guidelines

Germanium optics require special handling and cleaning procedures. Always wear gloves during handling to prevent contamination, and wash hands afterward. Avoid contact between Germanium dust and the eyes, skin, or clothing. When not in use, store optics sealed and covered at temperatures between 20°C and 25°C. Do not expose them to temperatures exceeding 100°C when in use.

Handling Guidelines

- Always wear [gloves](#) to prevent damage from skin oils.
- If Germanium dust is present, take the following precautions:
 - Wear safety glasses to protect eyes.
 - Use a dust mask or face mask to avoid inhalation.
 - Wear [gloves](#) to prevent skin contact.
- Maintain storage temperature between 20°C and 25°C with humidity below 30%.
- Wrap Germanium optics in a [lens cloth](#) or [pouch](#) and seal in a [container](#) when not in use.
- Germanium is brittle and heavy—always place it on soft surfaces and avoid dropping it.

Approved Cleaning Solvents

- Ethanol
- Isopropyl Alcohol
- Methanol
- Reagent-Grade Acetone
- Liquid CO₂
- [Shop Now](#)

Compatible Mounts