


TECHSPEC® 25mm VIS 0 Phase Correcting, Schmidt Prism



Stock **#13-805** **5 In Stock**

C\$917.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | C\$917.00 each |
| Qty 11+ | C\$733.60 each |
| Need More? | Request Quote |

Product Downloads

General

Schmidt Prism **Type:**

Physical & Mechanical Properties

41.3 **Height (mm):**

36.74 **Length (mm):**

±0.1 **Dimensional Tolerance (mm):**

| | |
|---|--|
| Protective as needed | Bevel: |
| 25.00 | Width (mm): |
| Optical Properties | |
| VIS 0° Phase Correcting | Coating: |
| N-BK7 | Substrate: <input type="checkbox"/> |
| 40-20 | Surface Quality: |
| 5.00 | Angle Tolerance (arcmin): |
| Right-Handed | Image Orientation: |
| Coating Specification: Entrance/Exit Faces: $R_{avg} \leq 0.4\%$ @ 425 - 675nm Roof: Photopic deviation $\delta p < 5\%$ | |
| 45 | Ray Deviation (°): |
| 400 - 700 | Wavelength Range (nm): |
| 1.00 | Power (fringes) @ 632.8nm: |
| 0.25 | Irregularity (fringes) @ 632.8nm: |

| | |
|------------------------------|------------------------------------|
| Regulatory Compliance | |
| View | Certificate of Conformance: |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- Ray Deviation of 45°
- Right Handed Image
- 5 Arcsecond Roof Angle Tolerance
- Combine with Half-Penta Prism to Create Schmidt-Pechan Prism

Schmidt prisms are ideal for creating a right handed image with a ray deviation of 45°. They are similar in function to [TECHSPEC® Amici Roof Prisms](#), however the 45° deviation makes Schmidt prisms especially useful in eyepiece assemblies and imaging systems requiring a path bend. The aluminized roof surfaces enhance the overall efficiency while the 5arcsecond roof angle tolerance increases the prism's resolution. TECHSPEC® Schmidt Prisms can be combined with [TECHSPEC® Half-Penta Prisms](#) to create a Pechan prism.

Technical Information





Schmidt Prism Tunnel Diagram

;