

TECHSPEC[®] 266nm 2.5X - 8X Research-Grade Variable Beam Expander



266nm 2.5X - 8X Research-Grade Variable Beam Expander, #87-565

Stock **#87-565** [CONTACT US](#)

-

1

+

C\$2,709⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$2,709.00 each
Qty 5-24	C\$2,387.00 each
Qty 25-99	C\$2,121.00 each
Need More?	Request Quote

Product Downloads

General	
Beam Expander	Type:
Variable Magnification	Style:
Physical & Mechanical Properties	
157.40	Length (mm):


483	Weight (g):
51	Housing Diameter (mm):
1	Maximum Input Beam Tilt (mrad):
Optical Properties	
15	Entrance Aperture (mm):
30	Exit Aperture (mm):
2.5X - 8X	Expansion Power:
Fused Silica (Corning 7980)	Substrate: ☐
>95 @ DWL	Transmission (%):
0 ±0.06	Angle of Incidence (°):
Laser V-Coat (266nm, 355nm)	Coating:
266	Design Wavelength DWL (nm):
Transmitted Wavefront, P-V: <3/4λ for Input Beam ≤4mm (2.5X-4X) ≤λ/2 for Input Beam ≤2mm (>4X)	
260 - 365	Wavelength Range (nm):
Coating Specification: R _{abs} <0.25% @ 265 - 267nm R _{abs} <0.25% @ 354 - 356nm R _{avg} <1.0% @ 260 - 365nm	
Damage Threshold, By Design: ☐ 2 J/cm² @ 10ns, 20 Hz, 266nm	
Non-Rotating Optics	Divergence Adjustment:
2 J/cm² @ 266nm, 10ns, 20Hz	Damage Threshold, Pulsed:

Threading & Mounting	
Mounting Threads: Input: Male C-Thread (1" x 32 TPI) Output: Male T-Thread (M42 x 0.75)	


Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details


- 1X– 3Xand 2X– 8XVariable Magnification
 - Non-Rotating Lenses Minimize Beam Wander
 - Compact Galilean Designs with Fixed Housing Length
 - [TECHSPEC® Draconis® Broadband Beam Expanders](#) Also Available
- TECHSPEC® Research-Grade Variable Beam Expanders (RVBX) are ideal for high power laser applications where magnification changes may be required, such as prototyping or R&D. TECHSPEC Research-Grade Variable Beam Expanders feature λ/4 transmitted wavefront, Galilean designs, and high laser damage threshold AR coatings to ensure maximum transmittance while minimizing ghost reflections. Additionally, these beam expanders use internal translation and focusing mechanisms to variable adjust magnification and laser divergence without affecting overall housing length. This compact design removes the need to make system accommodations for changes in length and eases system integration.
- TECHSPEC Research-Grade Variable Beam Expanders can be used to determine a system’s required beam magnification in the prototyping phase of development. [TECHSPEC® Draconis® Broadband Beam Expanders](#) are available for production or OEM implementation. Please contact our [Sales Department](#) for custom magnification requirements.



Technical Information



Design Wavelength	Stock No.	Fixed Overall Length A (mm)	Mounting Length E (mm)	Rotating Numeric Ring Length F (mm)	Rotating Alpha Ring Length G (mm)
355nm	#87-566	169.7	35.9	90.7	19.4
532nm	#87-567	169.3	31.5	70.4	43.7
Broadband VIS (633nm)	#87-569	169.3	31.5	70.4	43.7
Broadband NIR (785nm)	#87-570	169.3	31.5	70.4	43.7
1064nm	#87-568	169.3	31.5	70.4	43.7



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).