

[See all 13 Products in Family](#)

TECHSPEC[®]

30 to 25.4mm Cage Plate Reducing Ring



#85-706

Stock **#85-706** 8 In Stock

-

1

+

C\$42⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$42.00 each
Need More?	Request Quote

Product Downloads

General

Fixed

Function:

Circular/Cylindrical Tube

Type of Optics:

Physical & Mechanical Properties

30.0

Compatible Plate Inner Diameter (mm):

10.00

Length (mm):

25.4	Inner Diameter (mm):
Black Anodized Aluminum	Construction:
30 Dia.	Dimensions (mm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- English and Metric Post Adapters
- Customizable Blank Disks
- Reducing Rings

TECHSPEC® Cage System Accessories are additional components for customizing a cage system. Reducing rings are used to decrease the inner diameter of cage system plates, and feature a thru-hole that allows one of the set screws to pass from the plate, through the ring, to the optic or optical mount. For mounting directly to [posts](#), post adapter disks feature M6 or 1/4-20 tapped holes. 25mm diameter x 25mm length cage system post adapter disks can also be used to join a swivel plate pair. Blank disks are available to block optical paths, or to create customized mounts. Each blank disk features a 3mm diameter x 1mm deep centering hole for easy customization. Compatible with [#85-641](#) 30mm Side Access Plate, [#85-717](#) 25mm Interchangeable Optical Mount is equipped with a handle for easy insertion and removal from a cage setup.

Note: [#85-719](#) C-Mount Adapter fits within the inner diameter of 30mm cage system plates and features both male and female threading for easy integration with [TECHSPEC C-mount components](#).

Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [Interchangeable Optical Mount and Side Access Mounting Plate](#).