

[See all 2 Products in Family](#)

## 30mm Dia. x 100mm FL, 1064nm AR Coated, Gradium Lens

See More by [Lightpath®](#)



Stock #48-444 CLEARANCE **20+ In Stock**

⊖ 1 ⊕ C\$350<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$350.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Gradient Index Lens **Type:**

### Physical & Mechanical Properties

30.00 ±0.25 **Diameter (mm):**

1.00 **Centering (arcmin):**

27.00 **Clear Aperture CA (mm):**

Center Thickness CT (mm):  
6.00 ±0.1

Bevel:  
Protective as needed

## Optical Properties

Effective Focal Length EFL (mm):  
100.00 @ 546nm

Numerical Aperture NA:  
0.14

Back Focal Length BFL (mm):  
96.53

Focal Length Tolerance (%):  
±1

Coating:  
Laser V-Coat (1064nm)

Coating Specification:  
 $R_{avg} < 0.25\%$  @ 1064nm

Surface Quality:  
40-20

f#:  
3.7

Conjugate Distance:  
Infinite

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Reach 209:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

## Product Details

- Aspheric Performance
- Smaller Focused Spot Size
- Reduced Spherical Aberration

GRADIUM® lenses utilize advances in the manufacturing of axial gradient glass to improve lens performance. The process turns a glass of several SF layers into a single glass with a gradually changing index. The index may change by as much as 0.15 from the front surface to the back surface. This change in index allows for correction of system aberrations, especially spherical, yielding better images in infinite/finite imaging applications. GRADIUM® lenses are ideal for laser focusing applications, providing smaller spot sizes compared to the standard PCX counterpart. Two broadband antireflection coating options are available that cover a large range of visible and near-infrared laser wavelengths. For OEM and high volume coating options, please contact our [Applications Engineering Department](#) to discuss your requirements.

## Technical Information

