


35 x 35mm Opal Diffusing Glass



Stock #46-168 **14 In Stock**

C\$188^{AT}

ADD TO CART

Volume Pricing	
Qty 1-24	C\$188.47 each
Qty 25+	C\$151.37 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Opal Diffuser Type:

Physical & Mechanical Properties

Dimensional Tolerance (mm):

±0.76

35.00 x 35.00

Dimensions (mm):

Seamed

Edges:

2.50 ±0.2

Thickness (mm):

35.00

Width (mm):

35.00

Length (mm):

Optical Properties

Opal

Coating:

MilkyWhite 'Opal', 0.45 +0.35/-0.2mm in Thickness

Coating Specification:

Opal Glass

Substrate: □

Regulatory Compliance

Compliant

RoHS 2015:

[View](#)

Certificate of Conformance:

Compliant

Reach 247:


PRODUCT DETAILS

- Features a MilkyWhite 'Opal' Coating
- Even Diffusion Helps Create a Near Lambertian Source
- More Diffusion than a [Standard Ground Glass Diffuser](#)


Opal Diffusing Glass is similar to [ground glass](#), but with one surface flashed with a milky white "opal" coating to diffuse light evenly. It can be used to achieve a near Lambertian distribution. The level of diffusion in opal glass causes a large amount of scattering loss. Opal Diffusing Glass features more diffusion than a [Standard Ground Glass Diffuser](#). Due to the manufacturing process of the opal coating, the transmission may vary from one production to the next.

Note: Opal Glass material has been discontinued by the manufacturer and is available in limited quantities. Please consider [White Diffusing Glass](#) as an alternative. [Contact us](#) for more information.

TECHNICAL INFORMATION



Typical Spectral Transmission Efficiency Curve



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS
