

[See all 15 Products in Family](#)

**TECHSPEC® 355nm 1X - 3X Research-Grade Variable Beam Expander**



Research-Grade Variable Beam Expanders



Stock **#87-560** **2 In Stock**

- 1 + C\$2,107<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	C\$2,107.00 each
Qty 5-24	C\$1,855.00 each
Qty 25-99	C\$1,652.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Beam Expander **Type:**

Variable Magnification **Style:**

**Physical & Mechanical Properties**

172.30	<b>Length (mm):</b>
577	<b>Weight (g):</b>
58.2	<b>Housing Diameter (mm):</b>
<b>Optical Properties</b>	
10	<b>Entrance Aperture (mm):</b>
30	<b>Exit Aperture (mm):</b>
1X - 3X	<b>Expansion Power:</b>
<a href="#">Fused Silica</a> (Coming 7980)	<b>Substrate:</b> <input type="checkbox"/>
>95 @DWL	<b>Transmission (%):</b>
0 ±0.06	<b>Angle of Incidence (°):</b>
Laser V-Coat (266nm, 355nm)	<b>Coating:</b>
355	<b>Design Wavelength DWL (nm):</b>
<b>Transmitted Wavefront, P-V:</b> <math>N/4</math> @ 632nm for Input Beam $\leq 5\text{mm}$ (<math><0.45\lambda</math> @ 355nm for Input Beam $\leq 5\text{mm}$ )	
260 - 365	<b>Wavelength Range (nm):</b>
<b>Coating Specification:</b> R <sub>abs</sub> <math><0.25\%</math> @ 265 - 267nm R <sub>abs</sub> <math><0.25\%</math> @ 354 - 356nm R <sub>avg</sub> <math><1.0\%</math> @ 260 - 365nm	
<b>Damage Threshold, By Design:</b> <input type="checkbox"/> 1 J/cm <sup>2</sup> @ 10ns, 20Hz, 355nm	
Non-Rotating Optics	<b>Divergence Adjustment:</b>
1 J/cm <sup>2</sup> @ 355nm, 10ns, 20Hz	<b>Damage Threshold, Pulsed:</b>

<b>Threading &amp; Mounting</b>	
<b>Mounting Threads:</b> Input: Male C-Thread (1" x 32 TPI) Output: Male T-Thread (M42 x 0.75)	

<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details


For optimal performance, center the laser beam to the entrance lens and ensure that the beam is parallel to the beam expander's optical axis.

- 1X–3X and 2X–8X Variable Magnification
- Non-Rotating Lenses Minimize Beam Wander
- Compact Galilean Designs with Fixed Housing Length
- [TECHSPEC® Draconis® Broadband Beam Expanders](#) Also Available

TECHSPEC® Research-Grade Variable Beam Expanders (RVBX) are ideal for high power laser applications where magnification changes may be required, such as prototyping or R&D. TECHSPEC Research-Grade Variable Beam Expanders feature  $N/4$  transmitted wavefront, Galilean designs, and high laser damage threshold AR coatings to ensure maximum transmittance while minimizing ghost reflections. Additionally, these beam expanders use internal translation and focusing mechanisms to variable adjust magnification and laser divergence without affecting overall housing length. This compact design removes the need to make system accommodations for changes in length and eases system integration.


TECHSPEC Research-Grade Variable Beam Expanders can be used to determine a system's required beam magnification in the prototyping phase of development. [TECHSPEC® Draconis® Broadband Beam Expanders](#) are available for production or OEM implementation. Please contact our [Sales Department](#) for custom magnification requirements.





Design Wavelength	Stock No.	Fixed Overall Length A (mm)	Mounting Length E (mm)	Rotating Numeric Ring Length F (mm)	Rotating Alpha Ring Length G (mm)
355nm	<a href="#">#87-566</a>	169.7	35.9	90.7	19.4
532nm	<a href="#">#87-567</a>	169.3	31.5	70.4	43.7
Broadband VIS (633nm)	<a href="#">#87-569</a>	169.3	31.5	70.4	43.7
Broadband NIR (785nm)	<a href="#">#87-570</a>	169.3	31.5	70.4	43.7
1064nm	<a href="#">#87-568</a>	169.3	31.5	70.4	43.7

### 2X - 8X Variable Beam Expander



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).