

4" Fiber Optic Diffuse Axial Illuminators



4" Fiber Optic Diffuse Axial Illuminators (#53-381)



Stock **#53-381** CLEARANCE **1 In Stock**

-

1

+

C\$812⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$812.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
83% nominal	Packing Fraction (%):
Fiber Optic Light Guide	Type of Illumination:
Diffuse Axial	Geometry:

Physical & Mechanical Properties

	Construction:
Black Anodized Aluminum	

Optical Properties

	Numerical Aperture NA:
0.55 nominal	
	Fiber Diameter (µm):
50 (0.002" nominal)	
	Transmission Loss:
10% per ft. at 660nm	

Regulatory Compliance

	Reach 174:
Compliant	
	Certificate of Conformance:
View	

Product Details

- Wide-Angle, On-Axis, Diffused Illumination
- Factory Hardened, Industrial Rugged Packages
- View Objects Perpendicularly

Fiber Optic Diffuse Axial Illuminators provide wide angle, on-axis, diffused illumination housed in factory hardened, industrial rugged packages. These illuminators’ unique design allows the camera to view the object perpendicularly through the unit. As a result, highly reflective objects with uneven surfaces can reflect light to the camera from every point on their surface, eliminating glints and shadows. Fiber Optic Diffuse Axial Illuminators provide more uniform, diffused illumination than most lighting methods.

Available in two sizes, 2" x 2" and 4" x 4" square apertures, these sources provide full, even illumination over their entire aperture area. Illumination for the 2" model is provided using a standard ¼" light guide (not included). Illumination for the 4" model uses a specially designed quad-branch light guide (not included) that terminates into four 1/8" bundles. Both axial diffusers require a fiber optic illuminator and appropriate light guide adapter. Light Guide Adapters (not included) are required to mate the low-profile Fiber Optic Cable with Fiber Optic Illuminators. Platform, post and adapter shown in photo is for a suggested application only and not included.

Technical Information

