

[See all 23 Products in Family](#)

TECHSPEC® 40mm Dia., Enhanced Deep UV (DUV) Mirror



Precision Ultraviolet Mirrors

Stock **#18-747** **12 In Stock**

⊖ 1 ⊕ C\$543⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | C\$543.20 each |
| Qty 6-25 | C\$438.20 each |
| Qty 26-49 | C\$410.20 each |
| Need More? | Request Quote |

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

40.00 +0.0/-0.2 **Diameter (mm):**

Commercial Polish **Back Surface:**

Clear Aperture (%):

90

Parallelism (arcsec):

<30

Thickness (mm):

5.00 ±0.20

Optical Properties

Surface Flatness (P-V):

λ/10

Substrate:

Fused Silica (Corning 7980)

Surface Quality:

20-10

Coating Specification:

R_{avg} ≥92% @ 190 - 250nm

R_{avg} ≥83% @ 250 - 900nm

Coating:

Enhanced Aluminum (190-900nm)

Coating Type:

Metal

Angle of Incidence (°):

0

Design Wavelength DWL (nm):

190

Wavelength Range (nm):

190 - 900

Material Properties

Vacuum Compatibility:

10⁻⁷ Torr

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

REACH 241:

Compliant

Product Details


- 120nm and 190nm Design Wavelengths
- Average Reflectivity >85% Across Specified Range
- Enhanced Metallic Coatings for Broadband Reflectivity through the Visible Region

TECHSPEC® Precision Ultraviolet Mirrors are ideal for most commercially available light sources and are offered in both Deep UV (DUV) and Vacuum UV (VUV) enhanced coating options. The DUV coating offers excellent reflection from 190nm to the long-wave infrared (LWIR), while the VUV coating has optimized reflection from 120nm to the LWR. These mirrors are designed for 0° angle of incidence and feature an aluminum-based coating for low polarization sensitivity. TECHSPEC® Precision Ultraviolet Mirrors have an average reflectivity of greater than 85% across a specified range. The mirrors are available in diameters ranging from 5 to 50mm.


Note: The soft coating can be easily damaged by fingerprints and aerosols.


Technical Information

UV Reflectance Curve



Extended UV Reflectance Curve





Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts
