

[See all 13 Products in Family](#)

## 450 - 600nm, $\lambda/4$ Polymer Achromatic Waveplate



Polymer Waveplates (Retarders)

Stock **#88-198** [CONTACT US](#)

⊖ 1 ⊕ C\$464<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-5    | C\$464.80 each                |
| Qty 6-25   | C\$372.40 each                |
| Qty 26+    | C\$338.80 each                |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

Polymer Achromatic Waveplate **Type:**

### Physical & Mechanical Properties

25.00 **Diameter (mm):**

2.00 ±0.2 **Thickness (mm):**

3.00 **Parallelism (arcmin):**

+0.0/-0.2 **Dimensional Tolerance (mm):**

Birefringent Polymer Stack **Construction:**

## Optical Properties

$R_{avg} < 0.5\%$  @ 400 - 700nm **Coating:**

[E270](#) **Substrate:**

$\lambda/4$  **Retardance:**

$\pm 10$  @ 450 - 600 **Retardance Tolerance (nm):**

450 - 600 **Wavelength Range (nm):**

Achromatic **Retardance Order:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

## Product Details

- True Zero Order Waveplate Performance
- $\lambda/4$  and  $\lambda/2$  Retardance
- Available with Multiple Wavelengths or Achromatic Designs

Polymer Waveplates (Retarders) are durable, low-cost alternatives to quartz waveplates that feature a thin birefringent polymer film layered between two glass windows. The waveplates are designed to act as true zero order waveplates, providing stable performance over wavelength shift and wide angles of incidence. Due to their cemented construction and plastic birefringence material, these waveplates, or retarders, are not recommended for high power laser use or for extreme temperature shifts. Polymer Waveplates (Retarders) have either  $\lambda/4$  and  $\lambda/2$  retardance. They are offered in 405 to 650nm.

**Note:** Fast axis is marked on the edge of the glass.