

[See all 4 Products in Family](#)

# 50.8mm Dia., 5mm Thick, 2-13µm BBAR Coated, ISP Optics Zinc Selenide (ZnSe) Window | AR213-ZC-W-50-5

See More by [ISP Optics](#)



Stock #24-676 **CLEARANCE** 13 In Stock

⊖ 1 ⊕ C\$861<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$861.00 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

AR213-ZC-W-50-5 **Model Number:**

Protective Window **Type:**

### Physical & Mechanical Properties

43.18	<b>Clear Aperture CA (mm):</b>
50.80 +0.00/-0.13	<b>Diameter (mm):</b>
5.00 ±0.13	<b>Thickness (mm):</b>
<3	<b>Parallelism (arcmin):</b>
Protective as needed	<b>Bevel:</b>
85	<b>Clear Aperture (%):</b>
Fine Ground	<b>Edges:</b>
0.28	<b>Poisson's Ratio:</b>
67.2	<b>Young's Modulus (GPa):</b>
120.00	<b>Knoop Hardness (kg/mm<sup>2</sup>):</b>

## Optical Properties

BBAR (2000-13000nm)	<b>Coating:</b>
Zinc Selenide (ZnSe)	<b>Substrate:</b> <input type="checkbox"/>
2.631	<b>Index of Refraction (n<sub>d</sub>):</b>
60-40	<b>Surface Quality:</b>
R <sub>avg</sub> <3.0% @ 2 - 13µm R <sub>abs</sub> <6% @ 2 - 13µm	<b>Coating Specification:</b>
2000 - 13000	<b>Wavelength Range (nm):</b>
λ/20 @ 10.6µm	<b>Surface Flatness (P-V):</b>

## Material Properties

5.27	<b>Density (g/cm<sup>3</sup>):</b>
7.57	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 240:</b>

## Product Details

- Low Dispersion and Absorption from 0.6 – 18µm
- High Resistance to Thermal Shock
- Ideal for Thermal Imaging, FLIR, and Medical Systems

ISP Optics Zinc Selenide (ZnSe) Windows feature low absorption and low dispersion across a wide wavelength range from the visible to the infrared spectrum. This makes Zinc Selenide ideal for a wide array of infrared applications including thermal imaging, FLIR, and medical systems. Zinc Selenide (ZnSe) is a relatively soft material that scratches easily and it is not recommended in harsh environments because its Knoop Hardness is only 120. ISP Optics Zinc Selenide (ZnSe) Windows are particularly useful for 10.6µm CO<sub>2</sub> laser applications, due to its low absorption. These windows are available uncoated or with Broadband Anti-Reflection (BBAR) coating options for 2 - 13µm or 8 - 12µm for increased transmission.

**Note:** Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



