

## 50mm Dia. Left-Handed Uncoated Glass Circular Polarizer (CP42HE)



Stock #19-931 [CONTACT US](#)

⊖ 1 ⊕ **C\$113.40**

**ADD TO CART**

Qty 1-9

C\$113.40

Qty 10+

C\$102.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Coating:**  
Uncoated

**Diameter (mm):**  
50.00

**Substrate:**   
[Polymer Film CP42HE](#) Laminated Between Glass

**Operating Temperature (°C):**  
-40 to +80

**Thickness (mm):**  
2.00 ±0.10

**Transmission (%):**  
42 ±2

**Type:**  
Left-Handed Circular Polarizer

**Dimensional Tolerance (mm):**  
±0.20

**Construction:**  
Laminated Glass Polarizing Film

**Wavelength Range (nm):**  
400 - 700

**Polarization Efficiency (%):**  
>99.90

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 235:**  
[Compliant](#)

---