

**TECHSPEC® 532, 1064nm, 25.4mm, Dual-Band AR Fused Silica Window**



Stock #17-588 **14 In Stock**

⊖ 1 ⊕ C\$233.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$233.80 each
Qty 6-25	C\$186.20 each
Qty 26-49	C\$176.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Line Window **Type:**  
Glass **Type of Window:**

**Physical & Mechanical Properties**

22.86 **Clear Aperture CA (mm):**

25.40 +0.00/-0.10	<b>Diameter (mm):</b>
6.35 ±0.20	<b>Thickness (mm):</b>
<3	<b>Parallelism (arcmin):</b>
Fine Ground	<b>Edges:</b>

## Optical Properties

0	<b>Angle of Incidence (°):</b>
Dual-Band (532, 1064nm)	<b>Coating:</b>
532, 1064	<b>Design Wavelength DWL (nm):</b>
<a href="#">Fused Silica</a> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
10-5	<b>Surface Quality:</b>
R <sub>abs</sub> <0.25% @ 532nm, R <sub>abs</sub> <0.10% @ 1064nm	<b>Coating Specification:</b>
λ/10	<b>Surface Flatness (P-V):</b>
5J/cm <sup>2</sup> @ 532nm, 20ns, 20Hz; 15J/cm <sup>2</sup> @ 1064nm, 20ns, 20Hz	<b>Damage Threshold, By Design:</b> <input type="checkbox"/>

## Material Properties

7980 0F	<b>Fused Silica Grade:</b>
---------	----------------------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

### Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- 532 and 1064nm Dual-Band Anti-Reflection Coating
- 10-5 Surface Quality and λ/10 Surface Flatness
- Ideal for Nd:YAG Laser Systems
- [Uncoated Laser Window Substrates](#) Available

TECHSPEC® Dual-Band Anti-Reflection (AR) Laser Windows provide high performance AR coatings designed to be used in multi-wavelength laser applications. The anti-reflection coatings on both surfaces feature <0.25% reflection at 532nm and <0.1% reflection at 1064nm, significantly increasing laser throughput. These laser windows feature excellent thermal stability, precision grade λ/10 surface flatness, and 10-5 surface quality, ensuring minimal distortion to transmitted beams. TECHSPEC® Dual-Band Anti-Reflection (AR) Laser Windows are available in standard imperial sizes for convenient integration into existing laser systems and are ideal for Nd:YAG applications including those used in aesthetic laser systems. [Contact us](#) if your application requires a custom coating or design.

**Note:** Damage thresholds values are tested independently.

## Technical Information



