

## 5mm Diameter, Optical Cast Plastic IR Longpass Filter



Stock #12-762 **20+ In Stock**

⊖ 1 ⊕ C\$17<sup>15</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-49	C\$17.15 each
Qty 50-99	C\$14.00 each
Qty 100-249	C\$12.25 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Longpass Filter **Type:**

### Physical & Mechanical Properties

5.00 **Diameter (mm):**

0.20 **Diameter (inches):**

Thickness (mm):  
1.50 Nominal  
Dimensional Tolerance (mm):  
±0.3

## Optical Properties

Substrate:   
Thermoset ADC (CR-39®)  
Coating:  
Uncoated  
Color:  
Black  
Index of Refraction (n<sub>d</sub>):  
1.501 @ 20°C  
Transmission (%):  
>90 (typical)  
Abbe Number (v<sub>d</sub>):  
57.00

## Material Properties

Density (g/cm<sup>3</sup>):  
1.320 at 20°C

## Environmental & Durability Factors

Operating Temperature (°C):  
100 Continuous, 130 One Hour Max

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)



Reach 242:  
[Compliant](#)

## Product Details

- Lightweight Plastic
- Excellent Thermal and Chemical Resistance

Optical Cast Infrared (IR) Longpass Filters are ideal for blocking visible light while passing near infrared wavelengths. New plastic technology has produced filters with properties that can satisfy a variety of optical and environmental needs at half the weight of glass filters. Compared to similarly available transparent plastics, Thermoset ADC filters have the highest transmission and lowest haze, have at least 25-50 times greater abrasion resistance, and are resistant to all types of chemicals and solvents (acetone, acids, alkali, and alcohols). Optical Cast Infrared (IR) Longpass Filters have excellent thermal characteristics and are resistant to pits from hot sparks resulting from welding or grinding processes. The filters can also be easily drilled with high-speed carbide bits for all mounting types.

## Technical Information



## Compatible Mounts

