

[See all 96 Products in Family](#)

## 5µm Aperture Diameter, Unmounted, Precision Pinhole



Unmounted Precision Pinhole

Stock **#38-537** **1 In Stock**

⊖ 1 ⊕ C\$121<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	C\$121.80 each
Qty 6-10	C\$107.52 each
Qty 11+	C\$99.26 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Unmounted **Type:**

#### Physical & Mechanical Properties

9.5 **Outer Diameter (mm):**

Stainless Steel **Construction:**

5	<b>Fixed Aperture Diameter (<math>\mu\text{m}</math>):</b>
0.01 Nominal	<b>Thickness (mm):</b>
$\pm 1$	<b>Aperture Tolerance (<math>\mu\text{m}</math>):</b>
$\pm 50$	<b>Aperture Centration (<math>\mu\text{m}</math>):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Available in Aperture Mounts for a Secure Mechanical Support
- Pinhole Sized Ranging from 1 to 1,000 Microns
- [High Power Apertures](#) Available

### Unmounted Precision Pinholes

Precision Pinholes are high quality apertures centered to  $\pm 0.002''$  (50 microns). They are constructed of stainless steel and are  $3/8''$  (9.5mm) in diameter. Smaller diameter pinholes will reduce energy throughput, while larger diameter pinholes will pass more spatial noise. Precision pinholes have sizes ranging from 1 to 1,000 microns. Typical applications include leak detection, aerosol studies, holography, fiber optics guides, spatial filtering, research, and more.

Use the [Precision Pinhole Mount](#) to integrate unmounted pinholes into a variety of mechanical components easily.

### Mounted Precision Pinholes

Precision Pinholes are available in aperture mounts for secure mechanical support. The mounts also fit into various optical assemblies. Each 9.5mm diameter pinhole is sealed within a 25mm diameter black-anodized aluminum mount. The mount is clearly labeled with a pinhole aperture diameter for easy identification.

**Note:** Aperture Centering to Mount  $\pm 125$  microns.

Edmund Optics offers a wide selection of precision pinholes for leak detection, aerosol studies, holography, fiber optic guides, spatial filtering, research, and more. These pinholes are available in a range of diameters and are ideal for controlling light propagation. Each pinhole is manufactured using high-accuracy techniques, providing consistent circular aperture geometry and high edge quality. Available in both mounted and unmounted formats, these pinholes support a variety of optical setups, from experimental labs to industrial environments.

## Technical Information

