


# 5mW, 635nm Laser Bat Power ZAT, 60° X-Hair



Stock **#19-540** 1 In Stock

-

1

+

C\$499<sup>.80</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | C\$499.80 each                |
| Qty 10+        | C\$449.40 each                |
| Need More?     | <a href="#">Request Quote</a> |



| General                            |                             |
|------------------------------------|-----------------------------|
| Crosshair                          | Style:                      |
| 1M                                 | Laser Class - CDRH:         |
| Physical & Mechanical Properties   |                             |
| 162                                | Weight (g):                 |
| 124.00                             | Length (mm):                |
| Optical Properties                 |                             |
| 635.00                             | Wavelength (nm):            |
| Red                                | Color:                      |
| 60.00                              | Fan Angle (°):              |
| Up to 1,500mm                      | Focus Range (mm):           |
| Electrical                         |                             |
| 5                                  | Output Power (mW):          |
| Hardware & Interface Connectivity  |                             |
| 1 AA Battery (Not Included)        | Power Requirement:          |
| Free Space                         | Output Type:                |
| Environmental & Durability Factors |                             |
| IP40                               | Environmental Rating:       |
| Regulatory Compliance              |                             |
| <a href="#">View</a>               | Certificate of Conformance: |

## Product Details

- Bright Red 635nm Wavelength
- Line, Crosshair, or Dot Projection
- Battery Powered Operation with a Fixed Focus
- Sturdy, Metal Housing

Z-Laser ZAT Battery Powered Lasers are ideal for positioning and alignment applications. Their battery powered design provides maneuverability by removing the need for a fixed power supply. IP40 rated, shock proof, and vibration proof with a sturdy, metal housing makes these lasers excellent for harsh environments and repeated use. Z-Laser ZAT Battery Powered Lasers are suitable for use in industrial environments such as Automotive, Paper, Wood, Ceramic, and Metal. Available with 1 or 5mW output powers, the lasers utilize one AA battery (not included) ensuring easy maintenance and an extended lifetime.