

[See all 96 Products in Family](#)

## 600 μm Aperture Diameter, 1" OD Mounted, Precision Pinhole



Unmounted Precision Pinhole



Stock #90-307 **NEW** 2 In Stock

⊖ 1 ⊕ C\$124<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$124.60 each
Qty 6+	C\$111.02 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Mounted **Type:**

### Physical & Mechanical Properties

25.4 +0.000/-0.05 **Outer Diameter (mm):**

**Construction:**

Stainless Steel

600 **Fixed Aperture Diameter ( $\mu\text{m}$ ):**

0.03 Nominal **Thickness (mm):**

$\pm 5$  **Aperture Tolerance ( $\mu\text{m}$ ):**

$\pm 125$  **Aperture Centration ( $\mu\text{m}$ ):**

## Threading & Mounting

2.54 **Mount Thickness (mm):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

## Product Details

- Available in Aperture Mounts for a Secure Mechanical Support
- Pinhole Sized Ranging from 1 to 1,000 Microns
- [High Power Apertures](#) Available

### Unmounted Precision Pinholes

Precision Pinholes are high quality apertures centered to  $\pm 0.002"$  (50 microns). They are constructed of stainless steel and are  $3/8"$  (9.5mm) in diameter. Smaller diameter pinholes will reduce energy throughput, while larger diameter pinholes will pass more spatial noise. Precision pinholes have sizes ranging from 1 to 1,000 microns. Typical applications include leak detection, aerosol studies, holography, fiber optics guides, spatial filtering, research, and more.

Use the [Precision Pinhole Mount](#) to integrate unmounted pinholes into a variety of mechanical components easily.

### Mounted Precision Pinholes

Precision Pinholes are available in aperture mounts for secure mechanical support. The mounts also fit into various optical assemblies. Each 9.5mm diameter pinhole is sealed within a 25mm diameter black-anodized aluminum mount. The mount is clearly labeled with a pinhole aperture diameter for easy identification.

**Note:** Aperture Centering to Mount  $\pm 125$  microns.

Edmund Optics offers a wide selection of precision pinholes for leak detection, aerosol studies, holography, fiber optic guides, spatial filtering, research, and more. These pinholes are available in a range of diameters and are ideal for controlling light propagation. Each pinhole is manufactured using high-accuracy techniques, providing consistent circular aperture geometry and high edge quality. Available in both mounted and unmounted formats, these pinholes support a variety of optical setups, from experimental labs to industrial environments.

## Technical Information

