

**TECHSPEC® 6.0mm Diameter, N-BK7 Half-Ball Lens**



TECHSPEC® N-BK7 Half-Ball Lenses

Stock #45-935 **20+ In Stock**

⊖ 1 ⊕ C\$80<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | C\$80.50 each                 |
| Qty 11-49      | C\$72.10 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Half-Ball Lens **Type:**

**Physical & Mechanical Properties**

6.00 **Diameter (mm):**

±0.05 **Center Thickness Tolerance (mm):**

**Radius R (mm):**

3.00

Radius Tolerance ( $\mu\text{m}$ ):

+0.0/-1.5

Thickness (mm):

3.00

Diameter Tolerance ( $\mu\text{m}$ ):

$\pm 2.5$

## Optical Properties

Substrate:

N-BK7

Coating:

Uncoated

Wavelength Range (nm):

350 - 2200

## Regulatory Compliance

RoHS 2015:

Compliant

Reach 219:

Compliant

Certificate of Conformance:

[View](#)

## Product Details

- Fiber Coupling Half-Spheres
- Collimating Lenses

TECHSPEC® N-BK7 Half-Ball Lenses are ideal for applications such as fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems. Half-ball (hemispherical) lenses can be interchanged with full ball lenses if the physical constraints of an application require a more compact design. These collimating lenses are uncoated, with a wavelength range of 350-2200nm. TECHSPEC® N-BK7 Half-Ball Lenses are offered in diameters ranging from 0.50 to 10.00mm.

## Technical Information

