

[See all 69 Products in Family](#)

## TECHSPEC® 75mm Diameter x 3.3mm Thickness, Uncoated, BOROFLOAT® Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock #29-394 **20+ In Stock**

C\$52<sup>.50</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$52.50 each
Qty 6-25	C\$42.00 each
Qty 26-99	C\$39.20 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Protective Window **Type:**

Glass **Type of Window:**

### Physical & Mechanical Properties

**Clear Aperture CA (mm):**

67.50

Diameter (mm):

75.00 ±0.50

Thickness (mm):

3.30 ±0.2

Bevel:

Protective as needed

Clear Aperture (%):

≥90

Edges:

Ground and Seamed

Poisson's Ratio:

0.20

Young's Modulus (GPa):

64

Knoop Hardness (kg/mm<sup>2</sup>):

480.00

## Optical Properties

Coating:

Uncoated

Substrate:

[BOROFLOAT®](#)

Index of Refraction (n<sub>d</sub>):

1.472

Surface Quality:

80-50

Transmission (%):

90

Abbe Number (v<sub>d</sub>):

65.41

Wavelength Range (nm):

350 - 2000

Surface Flatness (P-V):

4 - 6λ

## Material Properties

Density (g/cm<sup>3</sup>):

2.23

Transformation Temperature (°C):

525

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

3.25 (+20 to +300°C)

## Environmental & Durability Factors

Operating Temperature (°C):

1 hour @ 500; >100 hours @ 450

Resistance to Temperature Difference (K):

Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term,  
>100 hrs: 80K

Thermal Shock (K):

Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 -  
15mm Thick: 150K

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)


## Product Details

- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



**Quote Your Size**

**Compatible Mounts**

---