

[See all 3 Products in Family](#)

TECHSPEC® 12.7mm Dia. Uncoated, Silicon, Laser Mirror



Stock #90-138 **NEW** [CONTACT US](#)

- 1 + C\$120.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$120.00 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror Substrate **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

90 **Clear Aperture (%):**

Commercial Polish **Back Surface:**

Diameter (mm):

12.70 +0.00/-0.10

3.18 ±0.10 **Thickness (mm):**

Optical Properties

40-20 **Surface Quality:**

N/A **Coating Specification:**

$\lambda/10$ **Surface Flatness (P-V):**

Uncoated **Coating:**

Optical Grade Silicon **Substrate:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Silicon Substrate for Thermally Demanding Ultrafast Setups
- $\lambda/10$ Surface Flatness and 40-20 Surface Quality
- Available In Standard Diameters for Coating Flexibility and System Integration

TECHSPEC® Silicon Laser Mirror Substrates feature a high-thermal-conductivity silicon substrate designed for thermally demanding high-power and ultrafast laser applications. Optimized for efficient heat distribution in challenging optical setups, these substrates help mitigate thermally induced wavefront distortion. Designed as a coating-ready platform, TECHSPEC® Silicon Laser Mirror Substrates provide a flexible foundation for custom broadband or low-dispersion mirror solutions. Available in 12.7mm, 25.4mm, and 50.8mm diameters, these mirrors offer flexibility for integration into a wide range of laser system configurations.