

# C4060, 1" Color, Teledyne DALSA Genie Nano 5GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie<sup>™</sup> Nano 5GigE Cameras (Front)



Stock **#16-031** **14 In Stock**

[Similar Cameras](#)

-

1

+

C\$4,190<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$4,190.20 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

## SPECIFICATIONS

### General

Color Camera

Type:

|                                                                         |                             |
|-------------------------------------------------------------------------|-----------------------------|
| Nano-5G-C4060                                                           | Model Number:               |
| Teledyne DALSA                                                          | Manufacturer:               |
| Genie Nano-5GigE                                                        | Camera Series:              |
| Color                                                                   | Spectrum:                   |
| Physical & Mechanical Properties                                        |                             |
| 59 x 44 x 42.6 (includes connectors and lens mount)                     | Dimensions (mm):            |
| 124                                                                     | Weight (g):                 |
| Full                                                                    | Housing:                    |
| Sensor                                                                  |                             |
| 450MB                                                                   | Image Buffer:               |
| 1"                                                                      | Sensor Format:              |
| 8.90                                                                    | Resolution (Megapixels):    |
| 68.00                                                                   | Frame Rate (fps):           |
| 4,112 x 2,176                                                           | Pixels (H x V):             |
| 3.45 x 3.45                                                             | Pixel Size, H x V (µm):     |
| 14.19 x 7.51                                                            | Sensing Area, H x V (mm):   |
| Sony IMX255                                                             | Imaging Sensor:             |
| Progressive Scan CMOS                                                   | Type of Sensor:             |
| Global                                                                  | Shutter Type:               |
| 8 bit                                                                   | Pixel Depth:                |
| Automatic, Programmable, or via External Trigger                        | Exposure Time:              |
| 76.46                                                                   | Dynamic Range (dB):         |
| GigE Vision v2.0                                                        | Machine Vision Standard:    |
| Electrical                                                              |                             |
| 9.4 - 9.6                                                               | Power Consumption (W):      |
| Hardware & Interface Connectivity                                       |                             |
| 5GigE (PoE)                                                             | Interface:                  |
| 5GigE, RJ45 with Screw Locks                                            | Connector:                  |
| Power over Ethernet (PoE) or via GPIO                                   | Power Supply:               |
| 2 digital input, 3 digital output                                       | GPIOs:                      |
| Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588) | Synchronization:            |
| Back Panel                                                              | Interface Port Orientation: |
| 10-pin Samtec                                                           | GPIO Connector Type:        |
| Threading & Mounting                                                    |                             |
| C-Mount                                                                 | Mount:                      |
| 1/4-20 with Tripod Mount Adapter <a href="#">#34-966</a>                | Mounting Threads:           |
| Environmental & Durability Factors                                      |                             |

|            |                             |
|------------|-----------------------------|
| -20 to +65 | Operating Temperature (°C): |
| -40 to +80 | Storage Temperature (°C):   |

Regulatory Compliance

|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|

PRODUCT DETAILS

- 5GBASE-T (5GigE) Ethernet Interface
- 3.2 to 12.4 Megapixel Sensors
- TurboDrive™ Technology for Data Transfer Speeds up to 985 MB/s
- Compact (32 x 44 x 59mm), Lightweight, and Robust Design



Teledyne DALSA Genie™ Nano 5GigE Cameras are available with a range of SONY Pregius sensors with resolutions from 3.2MP to 12.4MP. The 5GigE Ethernet interface provides data transfer speeds up to 5 times faster than the conventional GigE interface, which when combined with TurboDrive™ technology allows these cameras to achieve frame rates up to 187fps while retaining full image quality. The included Sapera CamExpert software provides a simple image acquisition interface with Sapera LT SDK libraries for OEM and system integration applications. Teledyne DALSA Genie™ Nano 5GigE Cameras are packaged in a compact, lightweight and robust all-metal housing, making them ideal for electronics inspection, industrial automation, and Intelligent Traffic Systems (ITS) applications. These cameras support the AIA GigE Vision Standard to facilitate easy integration into imaging systems.

**Note:** Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

**Sapera LT** is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.

CALIBRATION SERVICES