

# DALSA Genie Nano Cable Kit

See More by [Teledyne DALSA](#)



Dalsa Genie Nano Cable Kit, #34-967



Stock **#34-967** [CONTACT US](#)

⊖ 1 ⊕ C\$257<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$257.60 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

Camera Accessory **Type:**

**Contents of Kit:**  
12V Power Supply, 2m GigE Cable, and 2m Breakout Cable

**Note:**  
Included in Kit:  
· 12V Power Supply with Genie Nano Aux Connector

- (Samtec 10-pin), 4m
- RJ-45 Ethernet Cable, 2m
- GPIO Cable, Genie Nano Aux (Samtec 10-pin) to breakout Euroblock Connector, 2m

## Regulatory Compliance

[Compliant](#)

REACH 201:

[View](#)

Certificate of Conformance:

## Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne  
Authorized  
Distributor

Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.\* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

**Note:** Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

**Sapera LT** is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.