

Coherent® High-Sensitivity Thermopile Sensor PS19Q 1098341 | 1W Max Power

See More by [Coherent®](#)



Coherent® High-Sensitivity Thermopile Sensors

Stock **#12-418** [CONTACT US](#)

-

1

+

C\$2,912^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,912.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number: PS19Q Coherent Part Number: 1098341	
Type: Meter required	
Linearity (%): ±1	
Calibration Uncertainty (%): 1	
Cooling Method:	

Air	
2	Response Time (s):
Note: Includes a Wedged Quartz Window to Eliminate Thermal Background Radiation and Air Current Effects	
Compatible Meters: #35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412	

50mJ/cm ² (10ns, 1064nm)	Maximum Incident Energy Density:
-------------------------------------	----------------------------------

Physical & Mechanical Properties

19	Active Area Diameter (mm):
----	----------------------------

Optical Properties

514	Calibration Wavelength (nm):
-----	------------------------------

300 - 2000	Wavelength Range (nm):
------------	------------------------

0.3 - 2	Wavelength Range (µm):
---------	------------------------

Sensor

Thermopile	Type of Sensor:
------------	-----------------

Electrical

0.5	Maximum Incident Power Density (kW/cm ²):
-----	---

100µW - 1W	Power Range:
------------	--------------

1	Maximum Power (W):
---	--------------------

10µW	Power Resolution:
------	-------------------

Hardware & Interface Connectivity

2	Length of Cable (m):
---	----------------------

DB-25	Computer Interface:
-------	---------------------

Environmental & Durability Factors

Yes	Thermally Stabilized:
-----	-----------------------

Regulatory Compliance

Exempt	RoHS 2015:
------------------------	------------

Contains SVHC(s)	Reach 224:
----------------------------------	------------

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Broad Spectral Range with High Sensitivity and High Resolution
- Large Active Area Sensors up to 19mm in Diameter
- Flat Broadband Output with No Saturation above 1mW/cm²

Coherent® High-Sensitivity Thermopile Sensors are designed to have a broad spectral response to accommodate an array of lasers with different wavelengths. The large active area and high resolution of these thermopile sensors allows for accurate measurements of low-power lasers. A range of models are available to meet specific needs relating to thermal stability, background radiation, and air current effect. Coherent® High-Sensitivity Thermopile Sensors are designed to accurately measure the laser power of small laser diodes, HeNe lasers, and small ion lasers. Unique to this design, these sensors will not saturate when laser power exceeds 1mW/cm².