

[See all 8 Products in Family](#)

**TECHSPEC® CompactTL 65mm Working Distance Kit**



SilverTL™ Telecentric Lenses



Stock #29-141 [CONTACT US](#)

- 1 + C\$4,872<sup>00</sup>

**ADD TO CART**

|                |                               |
|----------------|-------------------------------|
| Volume Pricing |                               |
| Qty 1+         | C\$4,872.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

**Contents of Kit:**

- 8X, 65mm Compact: 63-744
- 4X, 65mm Compact: 63-736
- 2X, 65mm Compact: 63-734
- 1X, 65mm Compact: 63-733
- 0.5X, 65mm Compact: 63-741

**Optical Properties**

Working Distance (mm):

**Aperture (f#):**

8X, 65mm Compact: f/45  
4X, 65mm Compact: f/26.3  
2X Compact: f/17.3  
1X, 65mm Compact: f/18.6  
0.5X, 65mm Compact: f/9

## Sensor

**Maximum Sensor Format:**

2/3"

## Regulatory Compliance

**Certificate of Conformance:**

[View](#)

## Product Details

- Easy to Order Kits of Our Best Selling Telecentric Imaging Lenses
- Various Magnification and Working Distance Kits Available
- TECHSPEC [SilverTL](#), [VariMagTL](#), and [CompactTL](#)

TECHSPEC® Telecentric Imaging Lens Kits provide sets of TECHSPEC® [SilverTL](#), [VariMagTL](#), and [CompactTL](#) Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring telecentric lenses including machine vision, metrology, automotive and electronic inspection, measurement, and gauging. TECHSPEC® Telecentric Imaging Lens Kits offer various selections of magnifications and working distances within the product lines. The TECHSPEC® [SilverTL](#), [VariMagTL](#), and [CompactTL](#) lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- [SilverTL](#): Silver Telecentric, Metrology and Gauging
- [VariMagTL](#): Variable Magnification Telecentric, Adjustable Magnification That Can Be Locked with a Set Screw
- [CompactTL](#): Compact Telecentric, C-Mount Lenses for Machine Vision, Factory Floors, Assembly Lines