

[See all 78 Products in Family](#)

# Preloaded Norland Optical Adhesive NOA 65 Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock #55-157 **3 In Stock**

- 1 + C\$41<sup>.25</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-11	C\$41.25 each
Qty 12-19	C\$37.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

0.1	Size (oz):
65	Norland Number:
6 months	Shelf Life:
Barrel	Type:

**Typical Applications:**

More flexible adhesive for extra low strain applications. Suitable for cold blocking applications.

**Note:**

Contains 2g of adhesive

**Physical & Mechanical Properties****Size (cc):**

3.00

**Optical Properties****Index of Refraction (n<sub>d</sub>):**

1.52 @ 589nm

**Absorption Range (nm):**

350 - 380

**Material Properties****Glass Bonding:**

Good

**Metal Bonding:**

Good

**Plastic Bonding:**

Fair

**Viscosity (cps):**

1200

**Bonding Type:**

Glass to Glass/Metal

**Energy for Full Cure (J/cm<sup>2</sup>):**

4.5

**Environmental & Durability Factors****Durability:**

Flexible

**Regulatory Compliance****RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 253:**

[Compliant](#)

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

