

DUV Waveplate $\lambda/2$ 257nm 12.7mm Dia



Stock **#29-969** **7 In Stock**

-

1

+

C\$694^{.51}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$694.51 each
Qty 6+	C\$540.18 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Crystalline Waveplate

Type:

Configuration:
Air spaced; no mounting glue; no glue contacted
spacer between crystals

Physical & Mechanical Properties	
>7	Clear Aperture CA (mm):
12.70 +0.00/-0.25	Diameter (mm):
6.00	Thickness (mm):
Crystalline	Construction:
<3	Parallelism (arcsec):
Optical Properties	
Laser V-Coat (257nm)	Coating:
257	Design Wavelength DWL (nm):
Crystal Quartz	Substrate: 
$\lambda/2$	Retardance:
10-5	Surface Quality:
$\lambda/10$ @632.8nm	Transmitted Wavefront, P-V:
$\pm\lambda/100$ @20°C	Retardance Tolerance:
0.0001	Temperature Coefficient ($\lambda/^\circ\text{C}$):
R<0.2% @ 257nm	Coating Specification:
0	Retardance Order:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- 257nm and 266nm Deep UV Wavelengths Available
 - Ideal For Vacuum Compatible Applications
 - Non-Anodized Mount and Adhesive-Free Construction
- DUV Vacuum-Compatible Waveplates are mounted in an unanodized aluminum housing and feature adhesive-free construction for low outgassing in vacuum environments. These waveplates are optimized for >99.8 transmission at 257 or 266nm designed wavelengths, with $\lambda/2$ or $\lambda/4$ retardance options for each. Featuring a superior retardation tolerance and zero-order construction, these waveplates have increased bandwidth and lower sensitivity to temperature change. DUV Vacuum-Compatible Waveplates have the fast axis marked on the edge of the mount for easy identification and system integration. These waveplates are ideal for life-science and lithography applications which require a vacuum environment.