

[See all 36 Products in Family](#)

Genie Nano GPIO 10-pin Cable, 2m

See More by [Teledyne DALSA](#)



#16-032: Genie Nano GPIO 10-pin Cable, 2m



Stock **#16-032** **6 In Stock**

-

1

+

C\$110⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$110.60 each
Need More?	Request Quote

Product Downloads

General	
Camera Accessory	Type:
Physical & Mechanical Properties	
2	Length (m):
Hardware & Interface Connectivity	

	Length of Cable (m):
2	
	Connector:
Samtec 10-pin to open end	

Regulatory Compliance

	Certificate of Conformance:
View	

Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.