

TECHSPEC®

Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick



Stock #29-523 **20+ In Stock**

C\$512⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$512.40 each
Qty 6+	C\$488.60 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

12.70 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.10 **Thickness (mm):**

Commercial Polish **Edges:**

Bevel:

Protective as needed

Optical Properties

10-5 **Surface Quality:**

Coating Specification:
 $R_s > 99.50\%$ @ 830 - 1010nm @45° AOI
 $R_p > 99.50\%$ @ 840 - 997nm @45° AOI

GDD Specification:
 $0 \pm 50 \text{ fs}^2$ @ 830 - 1010nm @45° AOI (s-pol)
 $0 \pm 50 \text{ fs}^2$ @ 861 - 966nm @45° AOI (p-pol)

Surface Flatness (P-V):
λ/10

Design Wavelength DWL (nm):
830 - 1010

Damage Threshold, Reference: □
 0.75 J/cm^2 @ 920nm, 100-on-1, S-Polarization, 5Hz,
Pulse Duration 25fs, 350μm Dia.

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- High Femtosecond Laser Damage Threshold exceeding 0.75 J/cm^2 for 25fs Pulse Duration at 920nm
- > 99.5% Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors utilize an innovative design approach to maximize laser damage threshold for ultrafast pulses. These mirrors boast a near 0 fs^2 GDD over a broad spectral bandwidth, making them suitable for the most demanding ultrafast applications. A 45° angle of incidence makes them perfectly suitable as turn mirrors in advanced ultrafast laser systems. TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors' high reflectivity ensures minimal loss while maintaining ultrashort pulse durations. The outstanding high laser damage threshold (LDT) values exceeding 0.75 J/cm^2 for 25fs Pulse Duration at 920nm for these mirrors ensures they will perform even under exceptionally high ultrafast pulse energies.

Coating Curves