

[See all 104 Products in Family](#)

IDS U3-3560XCP-M-GL, USB 3.0, 1/2.6" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Cameras



Stock **#78-206** [CONTACT US](#)

-

1

+

C\$488^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	C\$488.60 each
Need More?	Request Quote

Product Downloads

Spectrum:	
Monochrome	
General	
Type:	
Monochrome Camera	
Model Number:	
U3-3560XCP-M-GL	
Manufacturer:	

IDS Imaging Development Systems	
uEye+ XCP	Camera Series:
Physical & Mechanical Properties	
29 x 29 x 17 (excludes connectors and lens mount)	Dimensions (mm):
61	Weight (g):
Full	Housing:
Sensor	
Not Specified	Image Buffer:
1/2.6"	Sensor Format:
2.30	Resolution (Megapixels):
102.00	Frame Rate (fps):
1,920 x 1,200	Pixels (H x V):
3.00 x 3.00	Pixel Size, H x V (µm):
5.76 x 3.6	Sensing Area, H x V (mm):
ON Semi AR0234	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
10 bit	Pixel Depth:
0.016ms - 2000ms	Exposure Time:
58.00	Dynamic Range (dB):
USB3 Vision	Machine Vision Standard:
Electrical	
0.5 - 1	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.0	Interface:
USB 3.0 micro-B, screwable	Connector:
Power over USB	Power Supply:
8-pin connector	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
Environmental & Durability Factors	
0 to +55	Operating Temperature (°C):
-20 to +60	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available

- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

Calibration Services

;