

JAI Fusion, 3200D-10GE, 1/1.8" 3.2MP, GigE Multispectral Camera



Stock **#29-170** 2 In Stock

-

1

+

C\$7,420^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$7,420.00 each
Need More?	Request Quote

Product Downloads

Spectrum:	
Multispectral	
General	
Type:	
Multispectral Camera	
Model Number:	
FS-3200D-10GE	
Manufacturer:	
JAI	
Camera Series:	
Fusion	

Physical & Mechanical Properties

62 x 62 x 86.5	Dimensions (mm):
270	Weight (g):
Full	Housing:

Sensor

1/1.8"	Sensor Format:
3.20	Resolution (Megapixels):
123.00	Frame Rate (fps):
2,048 x 1,536	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
7.1 x 5.3	Sensing Area, H x V (mm):
Sony IMX252	Imaging Sensor:
2 CMOS (Vis/NIR)	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
GigE Vision	Machine Vision Standard:

Electrical

10.4	Power Consumption (W):
------	------------------------

Hardware & Interface Connectivity

GigE (POE)	Interface:
RJ45 with Screw Locks	Connector:
Power Supply Required and Sold Separately. USA: #29-172 Europe: #29-172 Japan: #29-172 Korea: Not Available China: Not Available	Power Supply:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
12-pin Hirose	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
---------	--------

Environmental & Durability Factors

-5 to +45	Operating Temperature (°C):
-25 to +60	Storage Temperature (°C):

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Multispectral Camera Designed with Multiple Sensors
 - Designed for 400 – 670nm and 740 – 1000nm Wavelengths
 - Backwards Compatible 10GigE Interface
- JAI® Fusion Series Cameras are designed to image multiple wavebands at once, allowing for a more flexible imaging experience. Utilizing a prism as the camera input, the incoming light is separated and directed to the multiple

sensors with precision per-pixel alignment, providing excellent resolution of the individual wavebands. With a backwards compatible 10GigE interface, these cameras are easily integrated into existing imaging systems. JAI® Fusion Series Cameras have effective wavelength ranges of 400 to 670nm and 740 to 1000nm. These cameras are ideal for applications including surface inspection, NIR fluorescence, life sciences, and intelligent farming.

Note: These cameras require prism-corrected imaging lenses; alternatively, standard imaging lenses with zero rear protrusion can be used with reduced performance. Downloadable software is [available](#) online.

;