

# Laminated Wratten ND Filter 3.0 OD 25mm Dia



Stock **#29-318** 20+ In Stock

-

1

+

C\$140<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | C\$140.00 each                |
| Qty 11-25      | C\$113.40 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                                     |                |
|---------------------------------------------|----------------|
| Neutral Density Filter                      | Type:          |
| Supplied with protective film on both sides | Note:          |
| Physical & Mechanical Properties            |                |
| 25.00 +/- 0.25                              | Diameter (mm): |
| Optical Properties                          |                |

|                       |                                                                      |
|-----------------------|----------------------------------------------------------------------|
| 3                     | Optical Density OD (Average):                                        |
|                       | Substrate: <div>Wratten 2 Filter, One-Side Laminated onto PMMA</div> |
| Uncoated              | Coating:                                                             |
| 400-700               | Blocking Wavelength Range (nm):                                      |
| Regulatory Compliance |                                                                      |
| <a href="#">View</a>  | Certificate of Conformance:                                          |

## Product Details

- One-Side Laminated for Stability
  - Available in 25mm and 48mm Sizes
  - Kodak Filter No. 96
  - Lightweight Alternative to Traditional Glass ND Filters
- PMMA-Laminated Wratten ND Filters are ideal for light attenuation in image-forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. The laminated design offers additional stability and durability compared to traditional polyester/gelatin filters while remaining a lightweight alternative to traditional glass ND filters. These ND filters are available in 25mm or 48mm diameters and a thickness of 0.6mm. PMMA-Laminated Wratten ND Filters are uncoated and feature a blocking wavelength of 400 - 700nm with OD options of 0.1, 0.3, 0.5, 1.0, 2.0, and 3.0.