

[See all 68 Products in Family](#)

LUCID Vision Labs Triton™ TRI089S-MC, Sony IMX267, 8.9MP, Monochrome Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Triton™ Power over Ethernet (PoE) Cameras



Stock #13-725 **1 In Stock**

[Similar Cameras](#)

⊖ 1 ⊕ C\$1,309⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,309.00 each
Need More?	Request Quote

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

TRI089S-MC **Model Number:**

Lucid Vision Labs **Manufacturer:**

Triton™ **Camera Series:**

Physical & Mechanical Properties

29 x 29 x 45 (excludes connectors and lens mount) **Dimensions (mm):**

67 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1" **Sensor Format:**

8.90 **Resolution (Megapixels):**

13.70 **Frame Rate (fps):**

4,096 x 2,160 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (μm):**

14.13 x 7.45 **Sensing Area, H x V (mm):**

Sony IMX267 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

12 bit **Pixel Depth:**

30μs - 10s **Exposure Time:**

71.23 **Dynamic Range (dB):**

GigE Vision v2.0 **Machine Vision Standard:**

Electrical

3 (External Power Supply) **Power Consumption (W):**

3.5 (PoE)

Hardware & Interface Connectivity

GigE (PoE) **Interface:**

GigE, M12 **Connector:**

Power Supply:

Power Supply Required and Sold Separately:

USA: [#18-364](#)

Europe: [#18-364](#)

Japan: [#18-364](#)

Korea: Not Available

China: [#18-364](#)

GPIOs:

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

Synchronization:

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)

Interface Port Orientation:

Back Panel

GPIO Connector Type:

8-pin M8

Threading & Mounting

C-Mount **Mount:**

Mounting Threads:

1/4-20 with Tripod Mount Adapter [#11-474](#)

Environmental & Durability Factors

-20 to +55 **Operating Temperature (°C):**

-30 to +60 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Compact 29 x29 x45mm Form Factor
- Global, Rolling, or Polarized CMOS Sensors
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) Cameras provide exceptional price performance in a compact 29 x29mm form factor. These cameras are available with Sony's Pregius™ and Starvis™ imaging sensors with up to 24.5 megapixels of resolution, as well as Sony's polarized sensor. Each imaging sensor is actively aligned during manufacturing, ensuring sharp and crisp images even in the corners. Using the accessory IP67 lens tubes (sold separately), LUCID Vision Labs Triton GigE Power over Ethernet (PoE) Cameras can operate in harsh environments where dust or water are present up to IP67 thresholds. Triton cameras are ideal for automotive, process control, and food and beverage applications.

Calibration Services