

[See all 42 Products in Family](#)

## Model 1135P, 10mW Linear Polarization, Lumentum HeNe Laser



Lumentum High Performance Helium-Neon Lasers



Stock #62-727 [CONTACT US](#)

⊖ 1 ⊕ C\$2,618<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$2,618.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads



### General

Warm-Up Time (minutes):  
15

Manufacturer:  
Lumentum

Type of Laser:  
HeNe

Laser Class - CDRH:  
IIIb

1135P **Model Number:**

## Physical & Mechanical Properties

**Pointing Stability after Warm Up (mrad/°C):**  
After 15 min: <0.02

1.5 **Weight (lbs):**

19.13 **Length of Laser Head (inches):**

**Static Alignment:**  
Centered to Outer Cylinder:  $\pm 0.01''$   
Parallel to Outer Cylinder:  $\pm 1.0$  mrad

**Pointing Stability (mrad/°C):**  
From Cold Start, 25°: <0.1

1.74 **Diameter of Laser Head (inches):**

## Optical Properties

500:1 **Polarization:**

TEM<sub>00</sub> **Spatial Mode:**

632.80 **Wavelength (nm):**

$\pm 3$  **Beam Diameter Tolerance (%):**

$\pm 3$  **Beam Divergence Tolerance (%):**

Mean Power over 8 hrs:  $\pm 3$  **Maximum Drift:**

0.68 **Beam Diameter (mm):**

1.20 **Beam Divergence (mrad):**

Red **Color:**

>95% **Mode Purity (TEM<sub>00</sub>):**

## Electrical

10 **Output Power (mW):**

30 Hz - 10 MHz 1.0% **RMS Noise:**

320 **Longitudinal Mode Spacing, Nominal (MHz):**

10.0 **Minimum Output Power, TEM<sub>00</sub> (mW):**

## Hardware & Interface Connectivity

**Power Supply:**  
[#18-967](#) or [#18-970](#) (12VDC), [#18-968](#) (24VDC),  
[#11-381](#) or [#11-388](#) (110/220VAC)

Free Space **Output Type:**

## Environmental & Durability Factors

-40 to +70 **Operating Temperature (°C):**

0 to 100%, non-condensing **Operating Humidity:**

-40 to +150 **Storage Temperature (°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **REACH 241:**

## Product Details

110V or 220V power supplies sold separately. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993.

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

## Technical Information

### Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

