

[See all 22 Products in Family](#)

Red, 4" High Brightness LED Diffuse Axial Illuminator

See More by [Advanced Illumination](#)



Advanced Illumination Diffuse Axial LED Illuminators

Stock **#36-556** [CONTACT US](#)

-

1

+

C\$2,793^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,793.00 each
Need More?	Request Quote

Product Downloads

General	
DL225-100625IC	Model Number:
LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:
Diffuse Axial	Geometry:
	Illumination Mode:

Physical & Mechanical Properties

Weight (g):
1396.2

Optical Properties	
Refractive Index (n)	1.50
Transmittance (%)	95.0
Absorbance (A)	0.02
Color	Colorless
Fluorescence	None

Wavelength (nm):
625

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Operating Temperature (°C):	0 to +60
-----------------------------	----------

Compliant

Contains SVHC(s)	Reach 233:
------------------	------------

Note: Required 24V power supply #66-855. **Accessories for Advanced Illumination products** are available and sold separately. Units cannot be intensity controlled.

4" Diffuse Axial Illuminator

Technical drawing showing the front and top views of the 4" Diffuse Axial Illuminator. The front view (left) shows a rectangular unit with a total width of 177.6 and a total height of 102.2. The top view (right) shows a rectangular unit with a total width of 111.0 and a total height of 110.0. The top view also shows the positions of three circular features (likely ports or sensors) with dimensions: 38.1 (total width between outer features), 19.1 (width between inner features), and 8-M8 (thread size of the features). The front view shows a cable connection on the left side.

Units: mm