

[See all 9 Products in Family](#)

Sapphire SF NX 488nm, 50mW CDRH Laser Head

See More by [Coherent®](#)



Photo shows #70-113

Stock **#70-112** [CONTACT US](#)

1 **C\$12,404⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	C\$12,404.00 each
Need More?	Request Quote

Product Downloads

General

Warm-Up Time (minutes):
<5

Manufacturer:
Coherent®

Type of Laser:
Solid State

Laser Class - CDRH:
IIIb

Model Number:

Physical & Mechanical Properties

Pointing Stability after Warm Up (mrad/°C):

<5

Pointing Stability (μrad):

<30

Optical Properties

Spatial Mode:

TEM₀₀

Wavelength (nm):

488.00

Mode Quality, M²:

<1.1

Beam Diameter Tolerance (mm):

±0.05

Beam Diameter (mm):

0.70

Beam Divergence (mrad):

Full Angle: <1.2

Color:

Blue

Electrical

Output Power (mW):

50

Power Stability (%):

<2

RMS Noise:

≤0.25% (20Hz to 20MHz)

Hardware & Interface Connectivity

Power Supply:

Power Supply Required and Sold Separately.

USA: [#70-116](#)

Europe: [#70-116](#)

Japan: [#70-116](#)

Korea: [#70-116](#)

China: [#70-116](#)

Output Type:

Free Space

Environmental & Durability Factors

Operating Temperature (°C):

10 to 40

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Ultra-Narrow <1.5 MHz Linewidth
- Output Powers up to 200mW
- 488 and 532nm Wavelength Options

Coherent® Single Frequency Sapphire™ NX Laser Systems utilize Coherent®'s unique Optically Pumped Semiconductor Laser (OPSL) technology to provide a series of CW, single frequency, compact lasers. Available in 488 and 532nm wavelength options, these lasers provide a high-quality diffraction limited output beam and the single frequency design allows for extremely low noise. Flexible remote-control options for USB, RS-232, and analog connection all provide control options via the relevant ports on the CDRH Certified laser controller (sold separately). Coherent® Single Frequency Sapphire™ NX Laser Systems are ideal for applications that require an ultra-narrow linewidth such as Raman spectroscopy, interferometry, holography, metrology, and inspection. These lasers require [#70-116](#) Sapphire SF NX CDRH Certified Controller for power and control, sold separately.