

[See all 9 Products in Family](#)

Sapphire SF NX 532nm, 75mW CDRH Laser Head

See More by [Coherent®](#)



Photo shows #70-113

Stock **#70-114** [CONTACT US](#)

⊖ 1 ⊕ C\$12,180⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$12,180.00 each
Need More?	Request Quote

Product Downloads

General

<5	Warm-Up Time (minutes):
Coherent®	Manufacturer:
Solid State	Type of Laser:
IIIb	Laser Class - CDRH:
	Model Number:

Physical & Mechanical Properties

Pointing Stability after Warm Up (mrad/°C):

<5

Pointing Stability (μrad):

<30

Optical Properties

Spatial Mode:

TEM₀₀

Wavelength (nm):

532.00

Mode Quality, M²:

<1.1

Beam Diameter Tolerance (mm):

±0.05

Beam Diameter (mm):

0.70

Beam Divergence (mrad):

Full Angle: <1.3

Color:

Green

Electrical

Output Power (mW):

75

Power Stability (%):

<2

RMS Noise:

≤0.25% (20Hz to 20MHz)

Hardware & Interface Connectivity

Power Supply:

Power Supply Required and Sold Separately.

USA: [#70-116](#)

Europe: [#70-116](#)

Japan: [#70-116](#)

Korea: [#70-116](#)

China: [#70-116](#)

Output Type:

Free Space

Environmental & Durability Factors

Operating Temperature (°C):

10 to 40

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Ultra-Narrow <1.5 MHz Linewidth
- Output Powers up to 200mW
- 488 and 532nm Wavelength Options

Coherent® Single Frequency Sapphire™ NX Laser Systems utilize Coherent®'s unique Optically Pumped Semiconductor Laser (OPSL) technology to provide a series of CW, single frequency, compact lasers. Available in 488 and 532nm wavelength options, these lasers provide a high-quality diffraction limited output beam and the single frequency design allows for extremely low noise. Flexible remote-control options for USB, RS-232, and analog connection all provide control options via the relevant ports on the CDRH Certified laser controller (sold separately). Coherent® Single Frequency Sapphire™ NX Laser Systems are ideal for applications that require an ultra-narrow linewidth such as Raman spectroscopy, interferometry, holography, metrology, and inspection. These lasers require [#70-116](#) Sapphire SF NX CDRH Certified Controller for power and control, sold separately.