

## Schneider 80mm F-Mount Lens



Stock #34-235 **1 In Stock**

C\$2,597.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$2,597.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Product Family:**  
Schneider Large Format F-Mount VIS-NIR Lenses

**Note:**  
Optimized Working Distance: 403 - 2062mm

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**

56.90

Maximum Diameter (mm):

49.0

Outer Diameter (mm):

59.6

Weight (g):

280.00

Maximum Rear Protrusion (mm):

4.5

## Optical Properties

Field of View @ Min Working Distance (mm):

188 (35mm Sensor)

Horizontal Field of View, 35mm Sensor:

30.1°

Maximum Image Circle (mm):

60.00

Focal Length FL (mm):

80.00

Working Distance (mm):

403 - ∞

Aperture (f/#):

f/4.0 - 4/16

Distortion (%):

<0.8

Coating:

400 - 1000 BBAR

Lens Wavelength Range:

VIS-NIR Color Corrected

## Sensor

Maximum Sensor Format:

60mm (Image Circle)

Pixel Size (µm):

6.20

## Threading & Mounting

Filter Thread:

M43.0 x 0.75

Mount:

F-Mount

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 233:

[Compliant](#)

## Product Details

- Full Frame, 35mm (Covers 46mm Image Circle), F-Mount Lens
- Color Corrected for Spectral Range of 400 – 1000nm
- 28mm to 100mm Focal Length

Ideal for surface inspection and line scan applications, Schneider Large Format F-Mount VIS-NIR Lenses offer low distortion and uniform performance across the entire focal plane. Featuring a lockable focus and iris, these lenses have been optically corrected for the 400 – 1000nm wavelength range. They can cover up to 35mm format sensors (43.3mm sensor diagonal). Schneider Large Format F-Mount VIS-NIR Lenses has been highly toleranced to eliminate tilt in the image plane, providing repeatable and accurate results.