

Spatial Filter Movement



Stock #39-976 [CONTACT US](#)

- 1 + C\$924.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$924.00 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Black Anodized Aluminum **Construction:**

Pinhole: ± 3 in X-Axis and Y-Axis
Objective: 19 in Z-Axis **Travel (mm):**

9.5 **Aperture (mm):**

2.5 in Z-Axis **Accuracy (μm):**

Threading & Mounting

36 TPI 55° Whitworth (DIN Objective) **Mount:**

1/4-20 **Mounting Threads:**

50.8 TPI in X-Axis and Y-Axis **Leadscrew Thread:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**


Product Details

- X-Y Adjustable
- Pre-Mounted on a Gimbal Tilt-Table
- Open-Style Design

Our precision open-style spatial filter mechanism features a ball bearing, spring-loaded dual stainless rail objective movement with a micrometer drive. The pinhole mount accepts standard 3/8" (9.5mm) discs from our line of [Pinholes & Slits](#) and is X-Y adjustable via two fine thumbscrews. This entire assembly is mounted on a gimbal tilt-table with X-Y two-axis adjustment by two fine thumbscrews. A 1/4-20 tap hole on the gimbal platform base allows for easy mounting to posts or other positioning equipment. The [Understanding Spatial Filters](#) application note will help you select the appropriate components for your laser application.

Note: Spatial Filter does not operate with 5.5mm objective. Spatial Filter Movement is only compatible with the following objectives: DIN Achromatic 4X (#43-902), DIN Plan 4X (#67-706), and the JIS Achromatic 10X.

Technical Information



Input Beam Diameter (mm)	Magnification/Focal Length of Objective Lens (mm)	
	4X/31.04	10X/17.13
0.96	35µm	20µm
0.81	50µm	25µm
0.75	50µm	25µm
0.70	50µm	25µm
0.68	50µm	25µm
0.63	50µm	35µm
0.48	50µm	35µm