

TECHSPEC[®] UC Series Kit



UC Series: All lenses pictured may not be included in the kit. See "Contents of Kit" specification for included lenses.



Stock **#25-608** 1 In Stock

-

1

+

C\$2,030⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,030.00 each
Need More?	Request Quote

Product Downloads

General	
Series:	
UC Series	
Contents of Kit:	
8mm UC Series: 33-307	
12mm UC Series: 33-303	
16mm UC Series: 33-304	
25mm UC Series: 33-305	
35mm UC Series: 33-306	

Optical Properties

Working Distance (mm):
 8mm UC Series: 50 - ∞
 12mm UC Series: 100 - ∞
 16mm UC Series: 200 - ∞
 25mm UC Series: 200 - ∞
 35mm UC Series: 200 - ∞

Aperture (f/#):

8mm UC Series: f/1.8 - f/11
12mm UC Series: f/1.8 - f/11
16mm UC Series: f/1.8 - f/11
25mm UC Series: f/1.85 - f/16
35mm UC Series: f/1.85 - f/16

Aperture (f/#):

8mm UC Series: f/1.8 - f/11
12mm UC Series: f/1.8 - f/11
16mm UC Series: f/1.8 - f/11
25mm UC Series: f/1.85 - f/16
35mm UC Series: f/1.85 - f/16

Sensor

Maximum Sensor Format:	
8mm UC Series:	1/2"
12mm UC Series:	1/1.8"
16mm UC Series:	1/1.8"
25mm UC Series:	1/1.8"
35mm UC Series:	1/1.8"

Maximum Sensor Format:	
8mm UC Series:	1/2"
12mm UC Series:	1/1.8"
16mm UC Series:	1/1.8"
25mm UC Series:	1/1.8"
35mm UC Series:	1/1.8"

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

Product Details

- Easy to Order Kits of Our Best Selling Fixed Focal Length Imaging Lenses
- Full Product Line or Select Focal Lengths Kit Versions Available
- TECHSPEC C, UC, and HP Imaging Lenses are Also Sold Individually

TECHSPEC® Imaging Lens Kits provide sets of TECHSPEC C, UC, and HP Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring fixed focal lengths such as factory automation, machine vision, inspection, or rapid prototyping. TECHSPEC Imaging Lens Kits can be ordered as a full product line or as curated selections of focal lengths within the product line. The TECHSPEC C, UC and HP lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- **C Series:** Compact (C), FA Lenses for Machine Vision
- **UC Series:** Ultra-Compact (UC), High Resolution Lenses for Small Sensors
- **HP Series:** High Performance (HP), C-Mount Lenses for Machine Vision