

[See all 6 Products in Family](#)

## ZAP-IT® Laser Alignment Paper, 4 x 8", Box of 50 Sheets



Stock #90-709 **20+ In Stock**

⊖ 1 ⊕ C\$281<sup>40</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$281.40 each
Qty 6-24	C\$253.40 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Note:**  
Recommended Pulsed Width: 1ns to 30ms  
Recommended Power Level Range: 5 mJ/cm<sup>2</sup> to 20 J/cm<sup>2</sup>

### Physical & Mechanical Properties

0.009 Thickness (inches):

0.24 Thickness (mm):

4 x8 **Sheet Size (in):**

101.6 x203.2 **Sheet Size (mm):**

---

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

---

## Product Details

- Industrial Standard Beam Profile Viewing Paper
- Records Beam Shape, Divergence, Mode, and Intensity Profile of Pulsed Lasers
- Suitable for Broadband Sources from UV to IR

ZAP-IT® Laser Alignment Paper is designed to test the characteristics of pulsed laser sources from the ultraviolet to infrared. Beam characteristics are recorded by holding the ZAP-IT® Laser Alignment Paper in the beam path. ZAP-IT® Laser Alignment Paper is ideal for use in alignment applications or with [laser optics](#) including laser beam expanders, optical lenses, apertures, attenuators, or power meters. For continuous wave lasers, use a mechanical chopper, Q-switch, or manually switch the laser on and off rapidly to create short pulses.

**Note:** It may be difficult to see the beam characteristics when the input beam diameter is 1/4" (6.35mm) or less. If so, use a [beam expander](#) or [plano convex lens](#) to magnify the beam diameter. If using a plano convex lens, place ZAP-IT® Laser Alignment Paper at an image distance of 2.5 times longer than the focal length of the lens.

---